

Sterile 96-Well Plate Seal for Cell Culturing


RAPID Slit Seal

BioChromato Inc. has introduced a gamma sterilized version of its popular RAPID Slit Seal for scientists looking to eliminate solvent evaporation from samples when culturing cells in 96-well microplates.



Proven in labs worldwide,

RAPID Slit Seal is a proprietary self-closing microplate seal that returns to its original state even when punched with an HPLC or LC/MS autosampler. As a result, loss of volatile solvents from your valuable samples is eliminated.



Asynt Ltd

Unit 29 Hall Barn Road Industrial Estate Isleham Cambridgeshire United Kingdom CB7 5RJ
T: +44 (0)1638 781709 F: +44(0)1638 781706 enquiries@asynt.com www.asynt.com

In addition with RAPID Slit Seal insertion of pipette tips and sampling needles is easier and can be achieved without dragging saving you time and effort when dispensing or sampling.

Designed

to seal without using adhesive above microplate wells avoids the chance of sample contamination. In comparison to traditional sealing mats - RAPID Slit Seal also offers a way of reducing the cost of microplate sealing consumables.

For further information

on the gamma sterilized RAPID Slit Seals please visit <https://www.bicr.biz/product/consumables/rapid-slit-seal> or contact BioChromato Inc. on +81-466-23-8382 / europa@bicr.co.jp / northamerica@bicr.co.jp / enquiries@bicr.co.jp.

BioChromato Inc

Founded in 1983, BioChromato Inc is a respected Japanese manufacturer of unique high-quality products for chemical laboratories. Through its team of experienced technical experts and network of specialist distributors - BioChromato's aim is to enhance the efficiency of research and development through its development of problem-solving laboratory instruments and consumables.

Worldwide HQ**BioChromato Inc.**

1-12-19 Honcho, Fujisawa-shi,
Kanagawa-ken 251-0053
JAPAN

tel: +81-466-23-8382

email: enquiries@bicr.co.jp

web: <https://biochromato.com/>

Contact (Europe): europa@bicr.co.jp

Contact (North America): northamerica@bicr.co.jp

Asynt Ltd

Unit 29 Hall Barn Road Industrial Estate Isleham Cambridgeshire United Kingdom CB7 5RJ
T: +44 (0)1638 781709 F: +44(0)1638 781706 enquiries@asynt.com www.asynt.com